



The TCM3 is a step up from the TCM2.6 offering increased accuracy, extended tilt ranges of up to +/- 80° and a binary digital interface. Along with hard-iron calibration, the firmware also includes soft-iron correction algorithms, which allows for calibrating out most all magnetic anomalies, and thereby providing highly accurate compass heading in any environment. Improved built-in tilt calibration software makes it easier and faster to integrate the TCM3 into your system without sacrificing any accuracy or performance.

The TCM3 combines 3-axes of PNI Corporation's patented Magneto-Inductive (MI) magnetic sensors and a 3-axis MEMS accelerometer in a single module, offering unparalleled cost effectiveness and performance. MI sensors change inductance by 100% over a wide field measurement range. This variable inductance property is used in a cost and space efficient ASIC, incorporating a temperature and noise stabilized oscillator/counter circuit which is inherently free from offset drift.

## **Applications**

- High performance ROV navigation
- · GPS system integration
- Vehicle sensing & tracking
- Remote terrestrial antenna direction indicators
- Sonar targeting systems
- Survey equipment

## **Features**

- Improved compass heading accuracy: 0.5°
- High resolution compass heading: 0.1°
- High repeatability: 0.05°
- Extra wide tilt range: +/- 80°
- Multiple measurement modes: compass heading, magnetic field and 2-axis tilt
- Calibrated magnetic field measurement range: +/- 80 μT (+/- 0.8 Gauss)
- High resolution magnetic field measurement: 0.05 μT (0.0005 Gauss)
- Extended temperature range: -40° to 85°C
- Low Power: < 20 mA typical current draw
- Small size: 3.5 x 4.3 x 1.3 cm
- Advanced user calibration: hard-iron, soft-iron and tilt compensation
- Binary digital interface: RS-232

## **Ordering Information**

NAME PART NUMBER
TCM2.5 Module 12606
TCM2.5 Interface Kit 90011
TCM2.5 Evaluation Kit 90018

Interface kit includes: module, manual, evaluation software and 18" pigtail cable Evaluation kit includes: module, manual, evaluation software, 18" pigtail cable and 6ft finished DB-9 cable with power supply



|   | TCM3 Specifications   |  |
|---|---|--|
|   | TCM3  |  |
| Heading Specifications  |   |  |
| Accuracy with < 70° of tilt   | 0.5°  |  |
| Accuracy with > 70° of tilt   | 0.8°  | Deg RMS  |
| Resolution  | 0.1°  | Deg  |
| Repeatability (1)   | 0.05°   | Deg RMS  |
| Max Dip Angle   | 85°   | Deg  |
| Magnetometer Specifications   |   | J  |
| Calibrated Field Measurement Range  | ± 80  |  |
| Magnetic Resolution   | ±.05  | μΤ   |
| Magnetic Repeatability  | ± 0.1   | •  |
| Tilt Specifications   |   |  |
| Pitch Accuracy  | 0.2°  |  |
| The The Cardey  | 0.2° for pitch < 65°  | Deg RMS  |
| Roll Accuracy   | 0.5° for pitch < 80°<br>1.0° for pitch < 86°  | Deg HWS  |
| Tilt Range  | ± 80°   |  |
| Tilt Resolution   | < 0.01°   | Deg  |
| Tilt Repeatability (1)  | 0.05°   |  |
| Calibration   |   |  |
| Hard Iron Calibration   | Yes   |  |
| Soft Iron Calibration   | Yes   |  |
|   |   |  |
|   |   |  |
| Mechanical Specifications   |   |  |
| Mechanical Specifications  Dimensions (L x W x H)   | 3.5 x 4.3 x 1.3   | cm   |
|   | 3.5 x 4.3 x 1.3<br>12   | cm<br>grams                                    |
| Dimensions (L x W x H)  |   |  |
| Dimensions (L x W x H) Weight   | 12<br>Screw<br>Mounts/Standoffs   |  |
| Dimensions (L x W x H)  Weight  Mounting Options  | 12<br>Screw<br>Mounts/Standoffs<br>horizontal   |  |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  | 12<br>Screw<br>Mounts/Standoffs<br>horizontal   | grams  |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  | 12<br>Screw<br>Mounts/Standoffs<br>horizontal<br>9-pin  |  |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On   | Screw Mounts/Standoffs horizontal 9-pin < 210   | grams  |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  | Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  | grams<br>- mSec                                |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate   | Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1 20   | grams - mSec - samples/sec                     |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  | 12 Screw Mounts/Standoffs horizontal 9-pin  < 210 < 1 20 300 to 115200  | grams - mSec - samples/sec                     |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  | 12 Screw Mounts/Standoffs horizontal 9-pin  < 210 < 1 20 300 to 115200  | grams - mSec - samples/sec                     |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  | Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol   | grams - mSec - samples/sec - baud              |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  | Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol  3.6 to 5 V (Unregulated)   | grams - mSec - samples/sec - baud - VDC        |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  Typical Current Draw  (Continuous Output)   | Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol  3.6 to 5 V (Unregulated)  22   | grams - mSec - samples/sec - baud              |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  Typical Current Draw (Continuous Output)  Maximum  Typical  | Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol  3.6 to 5 V (Unregulated)  22  < 20   | grams - mSec - samples/sec - baud - VDC        |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  Typical Current Draw (Continuous Output)  Idle Mode (2)   | Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol  3.6 to 5 V (Unregulated)  22  < 20  14-18                                    | grams - mSec - samples/sec - baud - VDC        |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  Typical Current Draw (Continuous Output)  Idle Mode (2)  Sleep Mode   | Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol  3.6 to 5 V (Unregulated)  22  < 20  14-18                                    | grams  - mSec - samples/sec - baud  - VDC - mA |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  Typical Current Draw (Continuous Output)  Idle Mode (2)  Sleep Mode  Environmental Specifications   | 12 Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol  3.6 to 5 V (Unregulated)  22  < 20  14-18  0.6                            | grams - mSec - samples/sec - baud - VDC        |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  Typical Current Draw (Continuous Output)  Idle Mode (2)  Sleep Mode  Environmental Specifications  Operating Temperature                      | 12 Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol  3.6 to 5 V (Unregulated)  22  < 20  14-18  0.6                            | grams  - mSec - samples/sec - baud  - VDC - mA |
| Dimensions (L x W x H)  Weight  Mounting Options  Connector for RS-232 Interface  I/O Specifications  Latency from Power-On  Latency from Sleep Mode  Maximum Sample Rate  RS-232 Communication Rate  Output Formats  Power Specifications  Supply Voltage  Typical Current Draw (Continuous Output)  Idle Mode (2)  Sleep Mode  Environmental Specifications  Operating Temperature  Storage Temperature | 12 Screw Mounts/Standoffs horizontal  9-pin  < 210  < 1  20  300 to 115200  Binary High Performance Protocol  3.6 to 5 V (Unregulated)  22  < 20  14-18  0.6  -40° to 85°  -40° to 125° | grams  - mSec - samples/sec - baud  - VDC - mA |

<sup>(1)</sup> Repeatability is based on statistical data at  $\pm$  3 sigma limit about the mean. (2) Based on user settings